

**TECHSPEC® 0.1 OD 12.5mm Diameter, Reflective ND Filter**



Stock **#64-125** 3-4 DAYS

- 1 + **€34,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €34,00                        |
| Qty 6+                        |
| €27,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.50

Angle of Incidence (°):  
0

Optical Density OD (Average):  
0.1

|                                                                                               |
|-----------------------------------------------------------------------------------------------|
| <b>Substrate:</b> <div>Float Glass</div>                                                      |
| <b>Coating:</b><br>Surface 1: Inconel                                                         |
| <b>Reflection (%)</b> :<br>10.00                                                              |
| <b>Surface Quality</b> :<br>80-50                                                             |
| <b>Thickness (mm)</b> :<br>1.60 Nominal                                                       |
| <b>Transmission (%)</b> :<br>79.00                                                            |
| <b>Type</b> :<br>Neutral Density Filter                                                       |
| <b>Blocking Wavelength Range (nm)</b> :<br>400 - 700                                          |
| <b>Dimensional Tolerance (mm)</b> :<br>±0.5                                                   |
| <b>Clear Aperture (%)</b> :<br>80                                                             |
| <b>Neutrality</b> :<br>±3% of Transmission                                                    |
| <b>Note</b> :<br>Optical density values are average over specified blocking wavelength range. |
| <b>Surface Flatness (P-V)</b> :<br>4 - 6λ                                                     |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |