

0.5 OD, 25.4mm Dia., Reflective Neutral Density Filter



Stock **#27-928** CLEARANCE CONTACT US

- 1 + **€14,95**

ADD TO CART

Qty 1+
€14,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm): 25.40 ±0.3
Optical Density OD (Average): 0.5
Substrate: ☐ Borosilicate
Coating: Metallic Based ND
Thickness (mm): 1.00

Thickness Tolerance (mm): ±0.25
Transmission (%): 32.00
Type: Neutral Density Filter
Parallelism (arcmin): ±3
Dimensional Tolerance (mm): ±0.3
Clear Aperture (%): >90
Optical Density Tolerance (%): ±10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View