

100mm Diameter 0-1.5 OD, Circular ND Filter



Stock **#49-086** 3-4 DAYS

- 1 + **€316,00**

ADD TO CART

Qty 1-9
€316,00

Qty 10+
€284,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
100.00

Angle of Incidence (°):
0.00

Optical Density OD (Average):
0.04 - 1.5

Substrate: ☐

[B270](#)

Inner Diameter (mm):
8.3

Coating:
Variable

Thickness (mm):
2.00

Type:
Neutral Density Filter

Blocking Wavelength Range (nm):
400 - 700

Parallelism (arcmin):
3.00

Optical Density Tolerance (%):
±8

Coating Specification:
Continuously Variable Inconel from 0 - 310°

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)