

# 10mm Aperture UV/VIS Fiber Optic Collimator, SMA



Fiber Optic Collimator, SMA (SMA adapter inserted)



Stock **#88-181** [CONTACT US](#)

- 1 +

€370,00

ADD TO CART

|                               |         |
|-------------------------------|---------|
| Qty 1-10                      | €370,00 |
| Qty 11+                       | €327,00 |
| Volume Pricing                |         |
| <a href="#">Request Quote</a> |         |

ⓘ Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

Diameter (mm):  
15.88

Substrate: [Fused Silica](#) (Corning 7980)

|                                                                                                                                                                                                                   |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Type:</b><br>Fiber Collimator                                                                                                                                                                                  |
| <b>Wavelength Range (nm):</b><br>190 - 1250                                                                                                                                                                       |
| <b>Aperture Size:</b><br>10.0                                                                                                                                                                                     |
| <b>Compatible Fiber NA:</b><br>0.22                                                                                                                                                                               |
| <b>Connector:</b><br>SMA                                                                                                                                                                                          |
| <b>Fiber Diameter (µm):</b><br>compatible 400 to 800                                                                                                                                                              |
| <b>Focal Length FL (mm):</b><br>18.00                                                                                                                                                                             |
| <b>Housing Material:</b><br>Anodized Aluminum                                                                                                                                                                     |
| <b>Length (mm):</b><br>34.29                                                                                                                                                                                      |
| <b>Note:</b><br>Compatible with <a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a> Refocusing Assemblies |
| <b>Operating Temperature (°C):</b><br>-40 to 100                                                                                                                                                                  |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |