

1.0mm Dia, 1550nm DWL, 0.0mm WD, Uncoated, GRIN Lens



Stock **#64-529** 3-4 DAYS

- 1 + **€57,50**

ADD TO CART

Qty 1-10
€57,50

Qty 11+
€51,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
1.00 +0.00/-0.01

Effective Focal Length EFL (mm):
0.95

Substrate: ☐
Aluminosilicate Glass Embedded with Silver Ions

f/#:

0.95
Numerical Aperture NA: 0.53
Coating: Uncoated
Type: Gradient Index Lens
Wavelength Range (nm): 1310 - 1550
Clear Aperture (%) : 90.00
Gradient Constant (mm⁻¹): 0.653
Index of Refraction n_d - Center of Lens: 1.616
Length (mm): 2.41
Pitch: 0.25
Surface Quality: 40-20
Working Distance (mm): 0
Working Distance Tolerance (mm): ±0.01
Length Tolerance (%) : ±5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View