

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #67-380 3-4 DAYS



1



€50,50

ADD TO CART

Qty 1-10

€50,50

Qty 11+

€40,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
1.00

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type: Ball Lens
Wavelength Range (nm): 200 - 2200
Index of Refraction n_d : 1.458
Sphericity (μm): 0.625
Diameter Tolerance (μm): ± 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant