

TECHSPEC® 10mm, Enhanced Aluminum Coated, N-BK7 90° Specialty Mirror



Stock **#47-004** [CONTACT US](#)

⊖ 1 ⊕ **€122,50**

ADD TO CART

Qty 1-5
€122,50

Qty 6+
€98,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm): 9.0
Coating: Enhanced Aluminum (450-650nm)
Substrate: ☐ N-BK7

Surface Quality: 40-20
Type: Right Angle Mirror
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture (%): 90.00
Length of Hypotenuse (mm): 14.10
Length of Legs (mm): 10.00
Coating Specification: R _{avg} >95% @ 450 - 650nm
Wavelength Range (nm): 450 - 650
Surface Flatness (P-V): λ/8
Coating Type: Metal
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant