

10X Nikon CFI60 TU Plan Epi Infinity Corrected Obj

See More by [Nikon](#)



#58-516: 10XNikon CFI60 TU Plan Epi

Stock **#58-516** 3-4 DAYS

-

1

+

€1.247,00

ADD TO CART

Qty 1+

€1.247,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View (mm):
2.20

Horizontal Field of View, 1/2" Sensor:
0.64mm

Horizontal Field of View, 2/3" Sensor:
0.88mm

Focal Length FL (mm):
20.00

Model Number: MJE12100
Length excluding Threads (mm): 42.40
Magnification: 10X
Maximum Diameter (mm): 29
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.30
Mounting Threads: M25 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 1.0
Depth of Field (µm): 3.06
Field of View, 25 Diameter Field Eyepiece (mm): 2.5
Field of View, 22 Diameter Field Eyepiece (mm): 2.2
Working Distance (mm): 17.5
Weight (g): 125.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 22
Parfocal Length (mm): 60
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View