

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



TECHSPEC UV Fused Silica Right Angle Prisms

Stock #47-784 3-4 DAYS



1



€85,00

ADD TO CART

Qty 1-5

€85,00

Qty 6+

€68,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate:

[Fused Silica](#) (Corning 7980)

Surface Quality:

60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.10 Legs
Angle Tolerance (arcmin): ±5
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 17.70
Length of Legs (mm): 12.50
Pyramid Tolerance (arcmin): ±5
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/2

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View