

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Mounted Near-IR (NIR) Achromatic Lens Pairs

Stock #47-297 [CONTACT US](#)



1



€233,00

ADD TO CART

Qty 1-5

€233,00

Qty 6+

€186,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
22.0

Center Air Spacing (mm):
3.41

Substrate: ☐
[N-LAK22](#) / [N-SF6](#) / [N-LAK22](#) / [N-SF6](#)

Surface Quality: 40-20
Working f#: f/4.49
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Effective Focal Length EFL A (mm): 35.00
Effective Focal Length EFL B (mm): 100.00
Housing Diameter (mm): 30.0 +0.0/-0.10
Housing Length (mm): 34.00 ±0.2
Magnification: 1:2.86
Object Distance (mm): 25.00
Image Distance (mm): 89.50
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 750 - 1550

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View