

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Amici Roof Prisms

Stock #45-261 3-4 DAYS



1



€97,00

ADD TO CART

Qty 1-5

€97,00

Qty 6+

€76,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
13.00

Coating:
Uncoated

Substrate:
[N-BK7](#)

Surface Quality: 60-40
Type: Amici Roof Prism
Dimensional Tolerance (mm): +0/-0.1
Angle Tolerance (arcmin): ±5
Resolution (arcsec): 6.00
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View