

In order to provide more accurate inventory information, please select your shipping country.


Select Your Country/Region: European Union



SUBMIT



TECHSPEC Broadband Dielectric X/10 Mirrors



Stock #87-369 3-4 DAYS



1



€93,00

ADD TO CART

Qty 1-5

€93,00

Qty 6+

€74,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Dielectric Mirror (400-750nm)

Coating Specification:

R_{avg} >98% @ 400 - 750nm (0 - 45°)
R_{avg} >99% @ 400 - 750nm (0°)

Wavelength Range (nm):
400 - 750

Diameter (mm):
15.00 +0.00/-0.20

Surface Flatness (P-V):
λ/10

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Back Surface:
Commercial Polish

Surface Quality:
20-10

Coating Type:
Dielectric

Angle of Incidence (°):
0-45

Clear Aperture (%):
90

Edges:
Ground, 0.5mm max bevel

Parallelism (arcmin):
<0.5

Thickness (mm):
3.00 ±0.20

Type:
Flat Mirror

Damage Threshold, Reference: ☐
0.5 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 209:
[Compliant](#)

Certificate of Conformance:
[View](#)