

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #67-392 3-4 DAYS



1



€57,00

ADD TO CART

Qty 1-10

€57,00

Qty 11+

€44,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
1.50

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type: Half-Ball Lens
Wavelength Range (nm): 200 - 2200
Index of Refraction n_d : 1.458
Radius R (mm): 0.75
Radius Tolerance (μm): ± 2.5
Sphericity (μm): 0.625
Thickness Tolerance (μm): ± 35
Diameter Tolerance (μm): ± 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
