

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #65-794 3-4 DAYS



1



€201,00

ADD TO CART

Qty 1-9

€201,00

Qty 10+

€180,70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 1,600.00 ±2.5
Center Wavelength CWL Tolerance (nm): ±2.5
Full Width-Half Max FWHM (nm): 12.00 ±2.5
Full Width-Half Max FWHM Tolerance (nm): ±2.5
Minimum Transmission (%): >65
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: Clinical Chemistry
Blocking Wavelength Range (nm): 200 - 1800
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View