

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Standard Series

Stock #57-575 □ In Stock



1



€70,00

ADD TO CART

Qty 1-4

€70,00

Qty 5+

€61,70

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.0, Typical

Maximum Aperture (mm):
12.0

Outer Diameter (mm): 19.8
Construction: Anodized Aluminum Alloy, Anti-Reflection (AR) Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 10.00
Number of Leaves: 11.00
Thickness (mm): 5.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant