

TECHSPEC® 20mm Dia. x 80mm FL Uncoated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#49-964** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

€130,00

ADD TO CART

Qty 1-5

€130,00

Qty 6+

€104,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm): 80.00 @ 587.6nm
Back Focal Length BFL (mm): 77.95
Coating: Uncoated
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.61
Radius R₁ (mm): 36.68
Clear Aperture CA (mm): 19
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View