

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #32-990 3-4 DAYS

[Other Coating Options](#)



1



€30,50

ADD TO CART

Qty 1-9

€30,50

Qty 10+

€27,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-20.00
Substrate: N-SF11
f#: 1.00
Numerical Aperture NA: 0.50
Coating: Uncoated
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -20.55
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 19.00
Edge Thickness ET (mm): 5.03
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -31.82
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View