

**TECHSPEC® 2.0mm Diameter, Fused Silica Half-Ball Lens**



Stock **#67-393** 3-4 DAYS

- 1 + **€50,50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| €50,50                        |
| Qty 11+                       |
| €40,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
2.00

**Substrate:** ▢  
[Fused Silica](#) (Corning 7980)

**Coating:**  
Uncoated

|                                      |
|--------------------------------------|
| Type:<br>Half-Ball Lens              |
| Wavelength Range (nm):<br>200 - 2200 |
| Index of Refraction $n_d$ :<br>1.458 |
| Radius R (mm):<br>1.00               |
| Radius Tolerance (μm):<br>±2.5       |
| Sphericity (μm):<br>0.625            |
| Thickness Tolerance (μm):<br>±35     |
| Diameter Tolerance (μm):<br>±2.5     |

## Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |
| Reach 240:<br><a href="#">Compliant</a>             |