

TECHSPEC® 25 x 25mm Protected Silver, λ/4 Mirror



Stock **#49-195** 3-4 DAYS

⊖ 1 ⊕ **€75,00**

ADD TO CART

Qty 1-5
€75,00
Qty 6+
€60,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Dimensions (mm): 25.0 x 25.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) : 85
Edges: Fine Ground
Thickness (mm): 6.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Length (mm): 25.00
Width (mm): 25.00
Damage Threshold, Reference:  0.5 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant