

25mm Dia., Extended Hot Mirror



Extended Hot Mirrors

Stock **#46-386** ☐ In Stock

-

1

+

€66,00

ADD TO CART

Qty 1-9
€66,00
Qty 10+
€58,70
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°): 0.00
Coating: Hot Mirror, 0°
Diameter (mm): 25.00 ±0.25

Substrate:  BOROFLOAT®
Surface Quality: 80-50
Thickness (mm): 3.30
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Clear Aperture (%): ≥85
Edges: Ground
Coating Specification: R _{avg} ≥90% @ 750 - 1150nm R _{avg} ≥80% @ 1200 - 1600nm T _{avg} ≥85% @ 425 - 675nm
Wavelength Range (nm): 425 - 1600
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant