

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Convex Mirrors

Stock #87-677 3-4 DAYS



1



€57,00

ADD TO CART

Qty 1-5

€57,00

Qty 6+

€45,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-12.50

Center Thickness CT (mm):
5.00

Clear Aperture (%) : 90.00
Coating : Protected Silver (450-10000nm)
Coating Specification : R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating Type : Metal
Dimensional Tolerance (mm) : +0.0/-0.1
Edge Thickness ET (mm) : 1.65
Focal Length Tolerance (%) : ±2
Radius R (mm) : 25.0
Substrate : ☐ N-BK7
Surface Accuracy : λ/2
Surface Quality : 60-40
Thickness Tolerance (mm) : ±0.1
Type : Spherical Mirror
Wavelength Range (nm) : 500 - 10000

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant