

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Convex Mirrors

Stock #87-693 [CONTACT US](#)



1



€62,00

ADD TO CART

Qty 1-5

€62,00

Qty 6+

€49,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00

Focal Length FL (mm):  
-200.00

Center Thickness CT (mm):  
3.00

|                                                                                                                   |
|-------------------------------------------------------------------------------------------------------------------|
| <b>Clear Aperture (%)</b> :<br>90.00                                                                              |
| <b>Coating</b> :<br>Protected Gold (700-10000nm)                                                                  |
| <b>Coating Specification</b> :<br>R <sub>avg</sub> >96% @ 700 - 2000nm<br>R <sub>avg</sub> >96% @ 2000 - 10,000nm |
| <b>Coating Type</b> :<br>Metal                                                                                    |
| <b>Dimensional Tolerance (mm)</b> :<br>+0.0/-0.1                                                                  |
| <b>Edge Thickness ET (mm)</b> :<br>2.81                                                                           |
| <b>Focal Length Tolerance (%)</b> :<br>±2                                                                         |
| <b>Radius R (mm)</b> :<br>400.0                                                                                   |
| <b>Substrate</b> : <input type="checkbox"/><br><a href="#">N-BK7</a>                                              |
| <b>Surface Accuracy</b> :<br>λ/2                                                                                  |
| <b>Surface Quality</b> :<br>60-40                                                                                 |
| <b>Thickness Tolerance (mm)</b> :<br>±0.1                                                                         |
| <b>Type</b> :<br>Spherical Mirror                                                                                 |
| <b>Wavelength Range (nm)</b> :<br>700 - 2000                                                                      |

Regulatory Compliance

|                                                             |
|-------------------------------------------------------------|
| <b>RoHS 2015</b> :<br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance</b> :<br><a href="#">View</a> |
| <b>Reach 235</b> :<br><a href="#">Compliant</a>             |