

25mm FL, f/0.95, Schneider Fast C-Mount Lens



Stock #59-833 3-4 DAYS

[Similar Products](#)



1



€2.405,00

ADD TO CART

Qty 1+
€2.405,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
76.80

Iris Option:
Variable

Horizontal Field of View, 1/2" Sensor:
20°

Filter Thread:
M39 x 0.50

Maximum Image Circle (mm):

16.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Maximum Sensor Format: 1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/0.95 - f/11
Distortion (%): <3
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant

