

2.5mm FL, IR-Cut Filter at 650nm, f/2.5, Micro Video Lens



Stock #66-884 3-4 DAYS

- 1 + **€59,00**

ADD TO CART

Qty 1-49
€59,00
Qty 50+
€47,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
19.10

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
17.0

Maximum Image Circle (mm):

6.00
Horizontal Field of View @ Max Sensor Format: 115.8
Resolution, On-Axis: 63 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 48 lp/mm @ 20% Contrast
Resolution, Full Field: 30 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 2.50
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2.5
Distortion (%): -60 @ Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View