

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #53-711 3-4 DAYS



1



€46,50

ADD TO CART

Qty 1-24

€46,50

Qty 25+

€38,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
25.0 x 25.0

Cut-Off Wavelength (nm):
710.00

Substrate: ☐
[BOROFLOAT®](#)

Length (mm):

25.00
Operating Temperature (°C): <250
Coating: Traditional Coated
Index of Refraction n_d: 1.472
Surface Quality: 80-50
Thickness (mm): 1.10
Thickness Tolerance (mm): ±0.25
Type: IR Cut-Off Filter
Width (mm): 25.00
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥90
Edges: Seamed Edges
Coating Specification: Surface 1: T=50% @ 710±30nm, T _{avg} >85% @ 480 - 680nm, T _{avg} <10% @ 740 - 1200nm Surface 2: <i>N</i> /4 MgF ₂
Wavelength Range (nm): 480 - 1200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant