

2" x 2", ITO Coated EMI Shielded Plastic Window



Stock **#83-744** 3-4 DAYS

⊖ 1 ⊕ **€39,95**

ADD TO CART

Qty 1+

€39,95

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Bevel:
Protective as needed

Dimensions (mm):
50.80 x 50.80

Dimensions (inches):
2.00 x 2.00 ±0.010

Thickness (mm):
1.27

Thickness (inches):
0.05 ±0.005

Coating: S1: BBAR (450-650nm) S2: ITO Coating
Coating Specification: Surface 1: $R_{avg} < 1\%$ @ 450 - 650nm Surface 2: Clear Hard Coated
Construction: Silver Busbar Shielding Termination
Edges: Fine Ground
Substrate: PET
Type: Protective Window
Wavelength Range (nm): 450 - 650
Length (mm): 50.80
Width (mm): 50.80
Shielding Effectiveness @ 100MHz (dB): 49.00
Surface Resistivity (Ω/ Sq): 8.00
Visible Light Transmission VLT (%): >84

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View