

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



30.8mm Outer Diameter, Mounted Iris Diaphragm, #53-914

Stock #53-914 3-4 DAYS



1



€60,00

ADD TO CART

Qty 1-4

€60,00

Qty 5+

€53,10

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Mounted

Minimum Aperture (mm):
0.8

Maximum Aperture (mm):
12.0

Outer Diameter (mm): 30.8
Construction: Blackened Brass Housing, Stainless Steel Leaves, Stainless Steel Pin Actuators, Black Anodized Aluminum Mount
Inner Diameter (mm): 19.80
Lever Diameter (mm): 3.00
Lever Length (mm): 12.00
Mounting Threads: 8-32
Set Screw Thread: 4-40
Thickness (mm): 6.35

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)

