

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Aspherically Contoured Fresnel Lenses

Stock #43-011 □ In Stock



1



€43,50

ADD TO CART

Qty 1-10

€43,50

Qty 11+

€38,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
83.82

Substrate: □
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 3.0 x 3.0
Dimensions (mm): 76.2 x 76.2
Effective Diameter (inches): 2.5
Effective Focal Length EFL (inches): 3.30
Groove Density (grooves/inch): 125.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View