

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 30R/70T 12.5mm Dia., UV Plate Beamsplitter



TECHSPEC® UV Plate Beamsplitters

Stock #48-194 3-4 DAYS



1



€110,00

ADD TO CART

Qty 1-5

€110,00

Qty 6+

€88,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

45

Clear Aperture (%):

>85

Coating Specification:

Surface 1: R_{abs} = 30 ±5% @ 350nm, R_{avg} = 30 ±10%

over 250 - 450nm $T_{abs} = 70 \pm 5\%$ @ 350nm, $T_{avg} = 70 \pm 10\%$ over 250 - 450nm Surface 2: BBAR ($R_{avg} < 1\%$, $R_{abs} < 2\%$ over 250 - 450nm)

Construction:
Plate

Diameter (mm):
12.50

Dimensional Tolerance (mm):
+0.0/-0.2

Parallelism (arcmin):
<5

Reflection/Transmission Ratio (R/T):
30/70

Substrate: 
[Fused Silica](#) (Corning 7980)

Surface Flatness (P-V):
1λ

Surface Quality:
60-40

Thickness (mm):
2.00

Thickness Tolerance (mm):
±0.38

Type:
Standard Beamsplitter

Wavelength Range (nm):
250 - 450

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)