

35 x 35mm, 50R/50T, Plate Beamsplitter



Stock #45-325 ☐ In Stock

-

1

+

€61,00

ADD TO CART

Qty 1-9
€61,00

Qty 10+
€46,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR 1/λ MgF₂ @ 550nm

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 35.0 x 35.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 50/50
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 1.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant