

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



#68-684



Stock #68-686 CONTACT US

[Similar Products](#)



1



€1.470,00

ADD TO CART

Qty 1+

€1.470,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
17.0

Iris Option:
Variable

Length (mm):
49.00

Horizontal Field of View, 1/2" Sensor: 17.0mm - 10.4°
Filter Thread: M34 x0.50
Maximum Diameter (mm): 43.0
Weight (g): 160.00
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 35.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/2 - f/16
Maximum Distortion (%): <0.05%
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)