

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #43-582 3-4 DAYS



1



€191,00

ADD TO CART

Qty 1-9

€191,00

Qty 10+

€162,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate:

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy: λ/4
Diameter (inches): 3.0
Diameter (mm): 76.20 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 8.00
Effective Focal Length EFL (mm): 203.20
Radius of Curvature (mm): 406.40
Aperture (f/#): f/2.7
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View