

TECHSPEC® 3" Dia, 8" FL UV Enhanced Alum., Spherical Mirror



Stock **#43-584** 3-4 DAYS

⊖ 1 ⊕ **€270,00**

ADD TO CART

Qty 1-9
€270,00

Qty 10+
€229,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy: λ/4
Diameter (inches): 3.0
Diameter (mm): 76.20 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 8.00
Effective Focal Length EFL (mm): 203.20
Radius of Curvature (mm): 406.40
Aperture (f/#): f/2.7
Coating: Enhanced Aluminum (250-700nm)
Coating Specification: R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: 0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant