

TECHSPEC® 3" Dia. Protected Aluminum, λ /10 Flat ZERODUR®



Stock **#31-391-522** 3-4 DAYS

⊖ 1 ⊕ **€607,00**

ADD TO CART

Qty 1-10

€607,00

Qty 11+

€546,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 λ /10 (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 76.20 +0.0/-1.0
Substrate: 
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Clear Aperture CA (mm): 68.58
Note: Flatness is specified as Peak to Valley
Thickness (mm): 19.10 ±1.5
Thickness Tolerance (mm): ±1.5
Type: Flat Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference:  0.3 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant