

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #48-657 ☐ In Stock

☐ [Other Coating Options](#)



1



€52,50

ADD TO CART

Qty 1-9

€52,50

Qty 10+

€47,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):

40.00 @ 587.6nm
Back Focal Length BFL (mm): 35.13
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 8.70 ± 0.10
Edge Thickness ET (mm): 1.50
Radius R₁ (mm): 31.39
Clear Aperture CA (mm): 39
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View