

TECHSPEC® 4.0mm Diameter, Fused Silica Ball Lens



Stock **#67-385** ☐ In Stock

-

1

+

€44,50

ADD TO CART

Qty 1-10
€44,50
Qty 11+
€35,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.00

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type: Ball Lens
Wavelength Range (nm): 200 - 2200
Index of Refraction n_d : 1.458
Sphericity (μm): 0.625
Diameter Tolerance (μm): ± 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant