


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #69-887 [CONTACT US](#)



1



€166,00

ADD TO CART

Qty 1-5

€166,00

Qty 6+

€133,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
45

Cut-On Wavelength (nm):
450.00

Substrate: Fused Silica (Coming 7980)
Coating: Hard Coated
Reflection (%) >97, Average Polarization >95, Absolute Polarization
Reflection Wavelength (nm): 350 - 430
Surface Quality: 60-40
Thickness (mm): 1.05
Thickness Tolerance (mm): ±0.1
Transmission (%) >85, Average Polarization >80, Absolute Polarization
Transmission Wavelength (nm): 470 - 1600
Type: Dichroic Filter
Dimensional Tolerance (mm): +0.0/-0.2
Transmitted Wavefront Tolerance: λ/4
Cut-On Tolerance (%) ±2
Slope Factor (%) 3.00
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497ASection 4.5.4.2
Wavelength Range (nm): 350 - 1600
Wavelength Range (μm): 0.35 - 1.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant