

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #62-642

CONTACT US



1



€280,00

ADD TO CART

Qty 1+

€280,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:  
80-50

Type:  
Cold Mirror

Extension Length (mm):  
38.0

Dimensional Tolerance (mm):  
0.5

Type of Optics:  
45° Cold Mirror

Coating Specification:  
T<sub>avg</sub> ≥90% @ 800 - 1200nm  
R<sub>avg</sub> ≥95% @ 425 - 650nm

Thread Type:  
C-Mount (1" x 32 TPI)

Coating:  
Cold Mirror, 45°

Substrate: ☐  
[BOROFLOAT®](#)

Filter Included:  
[#64-449](#)

Regulatory Compliance

RoHS:  
[Compliant](#)

Certificate of Conformance:  
[View](#)