

4.6mm FL, High Resolution, f/2, Micro Video Lens



Stock #88-591 3-4 DAYS

- 1 + **€74,00**

ADD TO CART

Qty 1-49
€74,00
Qty 50+
€57,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm): 13.10
Maximum Diameter (mm): 12.0
Maximum Image Circle (mm): 6.50
Horizontal Field of View @ Max Sensor Format:

Resolution, On-Axis:
100 lp/mm @ 72.0% Contrast

Resolution, 0.7 Field:
100 lp/mm @ 38.0% Contrast

Resolution, Full Field:
100 lp/mm @ 29.0% Contrast

Note:
High Resolution

TV Distortion (%):
-27.1

Type:
M12 Imaging Lens

Focal Length FL (mm):
4.60

Maximum Sensor Format:
1/2.8"

Working Distance (mm):
400 - ∞

Mount:
M12 x 0.5 (S-Mount)

Aperture (f/#):
f/2

IR Cut Filter:
No

Lens Wavelength Range:
VIS

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)