

5.0" 625nm, LED Darkfield Illuminator

See More by [Advanced Illumination](#)



Stock **#66-793** [CONTACT US](#)

-

1

+

€975,00

ADD TO CART

Qty 1+

€975,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Height (mm):
46.2

Inner Diameter (mm):
55.0

Model Number:

RL3536B-660-IC
Mount: Standard and Barrel Mount
Operating Temperature (°C): 0 to +65
Outer Diameter (mm): 127.0
Mounting Threads: M4 x4
Wavelength (nm): 625.00
Working Distance (mm): 75 - 100
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 36.00
Number of Channels: 1.00
Field Coverage (mm): 32 - 38
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)