

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50/50.8mm Metric Tapped Platform



Stock #58-868 3-4 DAYS

1 €97,00

ADD TO CART

Qty 1-4

€97,00

Qty 5+

€87,70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Square or Rectangular

Size of Compatible Optics (mm):

12.7 - 50.8
Number of Adjustment Screws: 3
Thickness of Front Plate to C'bore (mm): 38.5
Travel (mm): Z-Axis: 8
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.4 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Compatible Post: M4 x0.7, 8-32
Thickness of Front Plate to Back Plate (mm): 23.0
Pointing Stability (μrad): 1.3
Plate Size (mm): 50.8 x 50.8
Plate Type: Metric, M6 Tapped

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View