

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #47-318 ☐ In Stock

-

1

+

€267,00

ADD TO CART

Qty 1-5

€267,00

Qty 6+

€213,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm):
150.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 139.87
Focal Length Specification Wavelength (nm): 880.00
Clear Aperture CA (mm): 49.00
Centering (arcmin): <1
Center Thickness CT (mm): 16.50 ±0.20
Center Thickness CT 1 (mm): 11.00 ±0.10
Center Thickness CT 2 (mm): 5.50 ±0.10
Radius R₁ (mm): 86.84
Radius R₂ (mm): -86.84
Radius R₃ (mm): -894.70
Edge Thickness ET (mm): 12.47
Substrate: N-LAK22 / N-SF6
Surface Quality: 40-20
f/#: 3.00
Numerical Aperture NA: 0.17
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 750 - 1550

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View