

50mm Diameter Mounted 0.04-3.0 OD, Circular Variable Neutral Density (ND) Filter



Mounted Circular Variable Neutral Density (ND) Filters

Stock #54-536 3-4 DAYS



1



€405,00

ADD TO CART

Qty 1-10

€405,00

Qty 11+

€364,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0.00

Optical Density OD (Average):
0.04 - 3.0

Substrate: ☐
[B270](#)

Inner Diameter (mm): 7.5
Coating: Variable
Outer Diameter (mm): 50.0
Surface Quality: 60-40
Thickness (mm): 1.52
Thickness Tolerance (mm): ±0.25
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Parallelism (arcmin): ±3
Dimensional Tolerance (mm): ±0.10 ID, ±0.20 OD
Optical Density Tolerance (%): ±5
Linearity (%): ±5
Coating Specification: Continuously Variable Inconel from 0 - 270°
Mount: Mounted

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View
