

In order to provide more accurate inventory information, please select your shipping country.


Select Your Country/Region: European Union



SUBMIT



Holographic Diffusers



Stock #56-056

CONTACT US



1



€802,50

ADD TO CART

Qty 1+

€802,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diffusing Angle (°):
0.2 x 10, 0.2 x 40, 2 x 10, 10 x 20

Diameter (mm):
50.00 ±0.1

Number of Diffusers:
4.00

Operating Temperature (°C):

-30 to +100 (Maximum of 240 Hours)

Substrate:

□

Polycarbonate

Type:
Holographic Diffuser

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
