

TECHSPEC®

50mm N-SF11 Uncoated Equilateral Prism



Equilateral Prisms

Stock **#49-432** ☒ In Stock



1



€344,00

ADD TO CART

Qty 1-5

€344,00

Qty 6+

€309,60

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:

Uncoated

Length of Face (mm):

50.00

Substrate: ☐

[N-SF11](#)

Length (mm): 50.00
Surface Quality: 40-20
Type: Equilateral Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Image Orientation: Dispersion
Wavelength Range (nm): 400 - 2500
Power (fringes) @ 632.8nm: 2.50
Irregularity (fringes) @ 632.8nm: 0.50

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View