

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #83-416 3-4 DAYS

-

1

+

 €17,75

ADD TO CART

Qty 1-10

€17,75

Qty 11+

€15,25

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
5.00 ±0.25

Coating:
Uncoated

Edges:
Ground Edges

Grit: ☐

Substrate: ☐
Float Glass

Thickness (mm):
1.60

Type:
Ground Glass Diffuser

Wavelength Range (nm):
350 - 2000

Note:
Sandblasted on first surface

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
