

40mm Max. Aperture, Iris Diaphragm



Stock **#36-624** 3-4 DAYS

⊖ 1 ⊕ **€118,00**

ADD TO CART

Qty 1-4
€118,00

Qty 5+
€104,40

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
2.5

Maximum Aperture (mm):
40.0

Outer Diameter (mm):

60.0
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 7.00
Lever Length (mm): 13.00
Number of Leaves: 12.00
Thickness (mm): 7.80

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant