

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Fiber Optic Collimator and Focuser Assemblies



Stock #67-725 3-4 DAYS



1



€180,00

ADD TO CART

Qty 1-10

€180,00

Qty 11+

€158,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):  
11.00 @ 633nm

Numerical Aperture NA:  
0.25

|                                                            |
|------------------------------------------------------------|
| <b>Substrate:</b> <a href="#">D-ZK3</a>                    |
| <b>Coating:</b><br>BBAR (600-1050nm)                       |
| <b>Coating Specification:</b><br>Rabs <1.0% @ 600 - 1050nm |
| <b>Surface Quality:</b><br>40-20                           |
| <b>Clear Aperture CA (mm):</b><br>5.50                     |
| <b>f#:</b><br>2.00                                         |
| <b>Bevel:</b><br>Protective bevel as needed                |
| <b>Connector:</b><br>SMA                                   |
| <b>Construction:</b><br>304L Stainless Steel Housing       |
| <b>Housing Diameter (mm):</b><br>11.00                     |
| <b>Housing Length (mm):</b><br>17.1                        |
| <b>Lightpath Lens Code:</b><br>354220                      |
| <b>Mount:</b><br>M11 x0.5                                  |
| <b>Type:</b><br>Fiber Collimator                           |
| <b>Wavelength Range (nm):</b><br>600 - 1050                |
| <b>Conjugate Distance:</b><br>Infinite                     |
| <b>Lens Included:</b><br><a href="#">#87-118</a>           |
| <b>Alignment Wavelength (nm):</b><br>633                   |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |