

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #31-402 ☒ In Stock



1



€325,00

ADD TO CART

Qty 1-5

€325,00

Qty 6+

€276,25

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
63.50 +0.00/-0.10

Effective Focal Length EFL (mm):
354.87

Focal Length Tolerance (%):
±1

Back Focal Length BFL (mm):

344.52
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 62.70
Centering (arcmin): 5.00
Center Thickness CT 1 (mm): 11.94
Center Thickness CT 2 (mm): 8.86
Radius R₁ (mm): 203.94
Radius R₂ (mm): -156.41
Radius R₃ (mm): -156.41
Radius R₄ (mm): -569.60
Edge Thickness ET (mm): 17.43
Substrate: ☐ N-BK7 / N-SF2
Surface Quality: 60-40
f/#: 5.6
Numerical Aperture NA: 0.09
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Construction: Unmounted, Cemented
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View