

## 58mm Max. Aperture, Iris Diaphragm



Stock #32-615 3-4 DAYS

⊖ 1 ⊕ **€189,00**

ADD TO CART

|         |
|---------|
| Qty 1-4 |
| €189,00 |

|         |
|---------|
| Qty 5+  |
| €167,30 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

|                                |
|--------------------------------|
| Type:<br>Unmounted             |
| Minimum Aperture (mm):<br>3.0  |
| Maximum Aperture (mm):<br>58.0 |
| Outer Diameter (mm):           |

|                                                                   |
|-------------------------------------------------------------------|
| 80.0                                                              |
| <b>Construction:</b><br>Brass Housing, Blue Tempered Steel Leaves |
| <b>Lever Diameter (mm):</b><br>3.00                               |
| <b>Lever Length (mm):</b><br>14.30                                |
| <b>Number of Leaves:</b><br>18.00                                 |
| <b>Thickness (mm):</b><br>8.00                                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Contains SVHC(s)</a>      |

---